



5.1.2 CS-RU18YKA CS-RU24YKA


<Top View>




<Side View>




<Front View>




<Side View>




<Bottom View>




<Remote Control>




<Rear View>



<Remote Control Holder>








Relative position between the indoor unit and the installation plate <Front View>



Unit: mm






5.2.3 CU-RU18YKA



Unit : mm

3-way valve at Gas side
(Low Pressure)
2-way valve at Liquid side
(High Pressure)

5.2.4 CU-RU24YKA



Unit : mm

3-way valve at Gas side
(Low Pressure)
2-way valve at Liquid side
(High Pressure)