



6.1.2 CS-PN18ZKA CS-PN24ZKA


<Top View>




<Side View>




<Front View>




<Side View>




<Bottom View>




<Remote Control>





<Rear View>



<Remote Control Holder>





Relative position between the indoor unit and the installation plate <Front View>




Unit: mm


6.2.3 CU-PN18ZKA CU-PN24ZKA



<Side View>




<Front View>



2-way valve at Liquid side
(High Pressure)
3-way valve at Gas side
(Low Pressure)

<Side View>



Unit: mm